

Vane probe thermo-anemometer LV 110 – LV 111 – LV 117

KEY POINTS

- Airflow calculation
- Automatic average
- Hold-min-max function
- Selection of units

TECHNICAL FEATURES

Measuring elements	Air velocity : Hall effect sensor Ambient temperature : NTC sensor
Display	4 lines, LCD technology. Sizes 50 x 36 mm 2 lines of 5 digits with 7 segments (value) 2 lines de 5 digits with 16 segments (unit)
Vane probe diameter	LV111 : Ø 14 mm / LV117 : Ø 70 mm LV110 : Ø 100 mm
Cable	Coiled, lg. 0.45 m, extension : 2.4 m
Housing	ABS, protection IP54
Keypad	5 keys
Conformity	Directives CEM 2004/108/CE and NF EN 61010-1
Power supply	4 batteries AAA LR03 1.5 V
Battery life	120 hours
Ambience	Neutral gas
Operating temperature (instrument)	From 0 to +50 °C
Operating temperature (probe)	From 0 to +50 °C
Storage temperature	From -20 to +80 °C
Auto shut-off	Adjustable from 0 to 120 min
Weight	390 g



SPECIFICATIONS


Models	Measuring units	Measuring range	Accuracy ¹	Resolution
Air velocity				
LV111 : Ø 14 mm	m/s, fpm, km/h	From 0.8 to 25 m/s	From 0.8 to 3 m/s : ±3% of reading ±0.1 m/s From 3.1 to 25 m/s : ±1% of reading ±0.3 m/s	0.1 m/s
LV110 : Ø 100 mm	m/s, fpm, km/h	From 0.3 to 35 m/s	From 0.3 to 3 m/s : ±3% of reading ±0.1 m/s From 3.1 to 35 m/s : ±1% of reading ±0.3 m/s	0.01 m/s 0.1 m/s
LV117 : Ø 70 mm	m/s, fpm, km/h	From 0.4 0 to 35 m/s	From 0.4 to 3 m/s : ±3% of reading ±0.1 m/s From 3.1 to 35 m/s : ±1% of reading ±0.3 m/s	0.1 m/s
Airflow				
All models	m ³ /h, cfm, l/s, m ³ /s	From 0 to 99 999 m ³ /h	±3% of reading ±0.03 * area (cm ²)	1 m ³ /h
Temperature				
All models	°C, °F	From -20 to +80 °C	±0.4 % of reading ±0.3 °C	0.1 °C

FUNCTIONS

- Airflow calculation
- Airflow calculation with cone (LV 110/117)
- Automatic average
- Selection of units (air velocity, airflow and temperature)
- Hold function
- Display of minimum and maximum values
- Configurable auto shut-off
- Backlight
- Detection of flow direction (LV 110/117)
- Selection of the type of cone
- Dimensions of rectangular and circular duct

¹All the accuracies indicated in this technical datasheet were stated in laboratory conditions, and can be guaranteed for measurements carried out in the same conditions, or carried out with calibration compensation


DIMENSIONS



OPERATING PRINCIPLES

Air velocity : Hall effect sensor

Rotation of the vane probe leads to a circular magnet of 8 poles. A dual Hall effect sensor, placed next to the magnet captures the signals of magnetic field polarity transition. The sensor signal is converted to electrical frequency and is proportional to the rotation velocity of the vane probe. Signal chronology allows to determine the rotation direction.



Thermometer : CTN probe

Negative temperature coefficient probes are thermistors with a resistance that decreases with temperature according to the equation below:

$$R_{(T)} = R_{(T_0)} e^{\left(\frac{\alpha}{100} \times (T_0 + 273.15)^2 \times \left(\frac{1}{T + 273.5} - \frac{1}{T_0 + 273.5} \right) \right)}$$

R_T = resistance sensor value at temperature T

$R(T_0)$ = resistance sensor value at reference temperature T_0

T and T_0 in °C

α and T_0 sensor specific constants

SUPPLIED WITH

Instruments are supplied with :

- LV 111 : vane probe Ø 14 mm
- LV 117 : vane probe Ø 70 mm
- LV 110 : vane probe Ø 100 mm
- Calibration certificate
- Transport case (ref : ST 110)



ACCESSORIES

CQ 15 : Magnetic protective housing



RTE : Telescopic extension, length 1m, with index at ±90°

K 25 – 85 : Airflow cones for anemometer LV 110



MT 51 : ABS transport case



MAINTENANCE

We carry out calibration, adjustment and maintenance of your instruments to guarantee a constant level of quality of your measurements. As part of Quality Assurance Standards, we recommend you to carry out a yearly checking.

GUARANTEE

Instruments have 1-year guarantee for any manufacturing defect (return to our After-Sales Service required for appraisal).

www.kimo.fr



EXPORT DEPARTMENT

Tel : + 33. 1. 60. 06. 69. 25 - Fax : + 33. 1. 60. 06. 69. 29

e-mail : export@kimo.fr

Distributed by :

زیست تجهیز پویش

(سهامی خاص)



آدرس: تهران، خ مطهری، خ فجر، ک افشار، پ ۱۶، ط ۱

تلفن: ۸۸۸۲۷۲۳۳ - ۸۸۸۲۶۸۷۵ فکس: ۸۸۸۲۶۷۹۱

پست الکترونیکی: info@PooyeshEnviro.ir